





Services

Technical Information

Indumax H CLS52

Inductive conductivity sensor with fast temperature measurement and hygienic design



Application

CLS52 conductivity sensors are intended specifically for use in the food industry. They are injection-moulded and consist of a highly resistant plastic material (PEEK) that meets the extremely exacting hygienic demands of the food industry.

- Alkali/acid concentration control in remaking
- Phase separation of product/water and product/product mixtures in pipe systems
- Monitoring and control of bottle cleaning systems
- Product monitoring in breweries, dairies and the beverage industry
- CIP system control
- Intended for use with the Liquisys M CLM223/253/223F and Mycom CLM153 transmitters; component of the Smartec S CLD132 measuring system

Your benefits

- Insensitive to electrode soiling and polarisation due to electrodeless, inductive measuring principle
- Suitable for foodstuffs applications and hygienically perfect thanks to jointless design without crevices
- Hydrodynamic sensor design ensures low flow resistance
- Maintenance-free due to no-contact measurement
- Versions with ultrafast temperature response $(t_{90} < 5 s)$ available
- Easy in-line installation is guaranteed by use of standard process connections commonly used in the food industry

quality certificate



Function and system design

Measuring principle

Inductive conductivity measurement

A generator (1) generates an alternating magnetic field in the primary coil (2) which induces a current in the medium (3). The strength of the induced current depends on the conductivity and thus the ion concentration of the medium. The current flow in the medium generates another magnetic field in the secondary coil (4). The resulting current induced in the coil is measured by the receiver (5) and processed to determine the conductivity.



Benefits of inductive conductivity measurement

- No electrodes, therefore no polarisation
- Accurate measurement in media or solutions with a high soiling degree and a tendency to deposition
- Complete galvanic separation of measurement and medium

Inductive conductivity measurement

- 1 Generator
- 2 Primary coil
- *3 Current flow in the medium*
- 4 Secondary coil
- 5 Receiver

Important properties Indumax H CLS52

Hygiene

The sensor, injection-moulded from highly chemically, mechanically and thermally resistant PEEK (polyether ether keton), does not have joints or crevices and is therefore hygienically safe.

- Temperature measurement and temperature compensation
- For applications requiring quick temperature measurement (e.g. CIP return, phase separation at various temperatures), the Pt 100 temperature sensor is installed in a stainless-steel thermal conductivity socket that is sealed by a Chemraz O-ring. This ensures extremely fast temperature response times ($t_{90} < 5$ s).
- For high-load applications, particularly for alternating thermal load due to very frequent sterilisation cycles or temperature shocks, the Pt 100 temperature sensor is embedded in the PEEK sensor body thus eliminating the need for a seal. This ensures a long service life. This sensor version can also be applied at underpressure.
- Process temperature

The use of special components and materials makes the sensor suitable for continuous exposure to temperatures of +125 °C. Short-time (max. 30 min.), it will work at +140 °C for sterilisation.

Process connections

The sensor is available with all process connections commonly used in hygienic applications.

Measuring system

A complete measuring system comprises:

- a CLS52 inductive conductivity sensor
- a transmitter, e.g. Mycom S CLM153



Measuring system example

- Indumax H CLS52 1
- 2 Mycom S CLM153 transmitter
- 3 Fixed cable (on the sensor)

Input

Measured values	Conductivity Temperature				
Cell constant k	$k = 5.9 \text{ cm}^{-1}$				
Measuring ranges	Conductivity Temperature	recommended range: 100 $\mu S/cm$ 2000 mS/cm (uncompensated) –5 +140 °C / -31 +284 °F			
Temperature measurement	Pt 100 (class A acc. to IEC 60751)				
Cable specification	Indumax H is supplied with a fixed cable. The connection to the transmitter can be extended using the CLK5 special measuring cable.				
		Cable			



Fixed cable / CLK5 special measuring cable

Cable length: max. 55 m / 180.46 ft total length

Performance characteristics

Temperature response time	t ₉₀ < 5 s t ₉₀ < 3.5 min	versions with stainless steel socket (CLS52-****A*) versions with encapsulated Pt 100 (CLS52-****B*)
Measured error	-5 +100 °C: > 100 °C:	\pm (10 µS/cm + 0.5 % of measured value) \pm (30 µS/cm + 0.5 % of measured value)

Installation

Installation instructions

The medium should flow through the conical measuring channel in the indicated direction.



Installation of the CLS52 in pipes with horizontal (middle) and vertical (right) flow directions

- a Sensor distance from the pipe wall
- *b* Indicator arrow for the flow direction
- c Flow direction
- 1 Welding neck
- 2 Pipe

Installation factor

In narrow installation conditions, the ion flow in the medium is affected by the pipe walls. This effect is compensated by the so-called installation factor. The installation factor can be entered in the transmitter or the cell constant can be corrected by multiplication with the installation factor to ensure correct measurement.

The value of the installation factor depends on the diameter and the conductivity of the pipe as well as the sensor's distance from the wall.

If the distance from the wall is sufficient (a > 15 mm, from DN 65), it is not necessary to consider the installation factor (f = 1.00).

If the distance from the wall is smaller, the installation factor increases in case of electrically insulating pipes (f > 1) and decreases in case of electrically conductive pipes (f < 1).

The installation factor can be measured using calibration solutions or it can be approximately determined from the diagram beside.



Dependance of installation factor f on wall distance a

- 1 Conductive pipe
- 2 Insulating pipe

Air set

To compensate residual coupling in the cable and between the two sensor coils, you must perform a zero calibration in air ("air set") before installing the sensor.

For further information, refer to the Operating Instructions of your transmitter.

Environment

Ambient temperature	−10 +70 °C / 14 158 °F	
Storage temperature	−25 +80 °C / −13 +176 °F	
Relative humidity	5 95 %	
Ingress protection	IP 67 / NEMA 6	

Process

Process temperature	−5 +125 °C / 23 257 °F
Sterilisation	140 °C / 4 bar (max. 30 min.) / 284 °F / 58 psi (max. 30 min.)
Process pressure	16 bar (up to 90 °C) / 232 psi (up to 194 °F) no underpressure permissible for sensor versions with stainless steel socket (CLS52-****A*)

Pressure/temperature load curve



A = short-time sterilisation (max. 30 min.)

Mechanical construction



Indumax H CLS52

- 1 Housing
- Temperature sensor 2
- 3 4 Process connection
- Flow opening

Design, dimensions



- Dairy pipe fitting DN 50 (DIN 11851) Α
- В SMS 2"
- С Internal thread G 11/2
- D Clamp 2" (ISO 2852)

- Varivent N DN 40 ... DN 125 Ε
- F Perlick 2" G
- APV DN 40 ... DN 100



Note! Clamp connection

Sensors with clamp connections can be fixed using sheet metal brackets or solid brackets.

Sheet metal brackets have a lower dimensional stability, uneven bearing surfaces causing point loads and sometimes sharp edges that can damage the clamp.

We **strongly** recommend to always use solid brackets because of their higher dimensional stability. Solid brackets may be applied over the total pressure-temperature range (see diagram on page 5).

Threaded connection

Sensors with threaded connections are supplied with expansion bellows (compensator) to be able to align them in flow direction. The two O-rings (Viton) of the expansion bellows have no sealing function and are not in contact with medium. The process is usually sealed off by PTFE tape on the G 1½ thread.

Chemical durability

Medium	Concentration	РЕЕК	1.4435 (AISI 316L)	Chemraz	EPDM
Caustic soda NaOH	0 10 %	20 100 °C / 68 212 °F	20 90 °C / 68 194 °F	20 100 °C / 68 212 °F	20 100 °C / 68 212 °F
	0 50 %	20 100 °C / 68 212 °F	20 90 °C / 68 194 °F	20 100 °C / 68 212 °F	20 60 °C / 68 140 °F
Nitric acid HNO ₃	0 10 %	20 100 °C / 68 212 °F	20 100 °C / 68 212 °F	20 100 °C / 68 212 °F ¹	20 °C / 68 °F
	0 25 %	20 40 °C / 68 104 °F	20 100 °C / 68 212 °F	20 100 °C / 68 212 °F ¹	not suitable
Phosphoric acid H ₃ PO ₄	0 10 %	20 100 °C / 68 212 °F	20 100 °C / 68 212 °F	20 100 °C / 68 212 °F	20 80 °C / 68 176 °F
	0 30 %	20 100 °C / 68 212 °F	20 85 °C / 68 185 °F	20 100 °C / 68 212 °F	20 80 °C / 68 176 °F
Sulphuric acid H ₂ SO ₄	0 2.5 %	20 100 °C / 68 212 °F ¹	20 70 °C / 68 158 °F	20 100 °C / 68 212 °F	20 30 °C / 68 86 °F
	0 30 %	20 100 °C / 68 212 °F ¹	not suitable	20 100 °C / 68 212 °F	20 30 °C / 68 86 °F

1) slight affect possible

No responsibility is taken for the correctness of this information.

Ordering information

Product structure		Approval					
Indumax H CLS52		A1	Standard				
			Version				
			MV1	Dairy pip	oe fitting	g DN 50, DIN 11851	
			CS1	Clamp 2" fitting, ISO 2852			
		GE1 Internal thread G 1½				G 1½	
			VA1 Varivent N connection DN 40 125				
			AP1 APV connection DN 40 100				
		PL1 Perlick adapter					
			SMS	AS SMS 2" connection			
				Tempe	erature	e sensor insert	
				A S	Stainles	s steel socket 1.4435 (AISI 316L), Chemraz seal, fast temperature measurement	
				B PEEK encapsulated for high loads			
					Cable	length	
					1	5 m / 16.41 ft cable	
				1	2	10 m / 32.81 ft cable	
				:	3	20 m / 65.62 ft cable	
	CLS52-					complete order code	

Accessories

Measuring cables	□ CLK5 measuring cable Extension cable for connecting CLS52 and transmitter via the VBM junction box, sold by the metre; order no. 50085473						
	□ Junction box VBM for cable extension, with 10 terminals, IP 65 / NEMA 4X						
	Cable entry Pg 13.5 Cable entry NPT ½"	Order no. 50003987 Order no. 51500177					
Calibration solutions	 Precision solutions, traceable to SRM conductivity measurement systems ac CLY11-B 149.6 µS/cm (reference temperatu Order no. 50081903 CLY11-C 1.406 mS/cm (reference temperatu Order no. 50081904 CLY11-D 12.64 mS/cm (reference temperatu Order no. 50081905 CLY11-E 107.0 mS/cm (reference temperatu Order no. 50081906 	 Precision solutions, traceable to SRM (standard reference material) by NIST, for qualified calibration of conductivity measurement systems according to ISO 9000, with temperature table CLY11-B 149.6 µS/cm (reference temperature 25 °C / 77 °F), 500 ml / 0.13 US.gal. Order no. 50081903 CLY11-C 1.406 mS/cm (reference temperature 25 °C / 77 °F), 500 ml / 0.13 US.gal. Order no. 50081904 CLY11-D 12.64 mS/cm (reference temperature 25 °C / 77 °F), 500 ml / 0.13 US.gal. Order no. 50081905 CLY11-E 107.0 mS/cm (reference temperature 25 °C / 77 °F), 500 ml / 0.13 US.gal 					
Related products	 Indumax P CLS50 Highly resistant inductive conductive applications; for ordering information, see Techr Smartec S CLD132 Measuring system for conductivity for ordering information, see Techr 	vity sensor for standard, hazardous and high-temperature ical Information TI 182C/07/en; order no. 50090385 and concentration measurement in the food industry; ical Information TI 207C/07/en; order no. 51501593					

Documentation

Transmitters	 Mycom S CLM153, Technical Information TI 234C/07/en; order no. 51503792 Liquisys M CLM223/253, Technical Information TI 193C/07/en; order no. 51500279 Liquisys M CLM223F, Technical Information TI 237C/07/en; order no.51505427
Calibration solutions	□ Precision calibration solution CLY11. Technical Information TI 162C/07/en; order no. 50086574

International Head Quarters

Endress+Hauser GmbH+Co. KG Instruments International Colmarer Str. 6 79576 Weil am Rhein Deutschland

Tel. +49 76 21 9 75 02 Fax +49 76 21 9 75 34 5 www.endress.com info@ii.endress.com

TI167C/07/en/07.04 50086110 FM+SGML 6.0 / ProMoDo / Printed in Germany / DT



People for Process Automation